♦ THOMSON-CSF LASER DIODES

Device type:

TH-C1720-F6

Serial number : 10045

Date: 09/02/2001

Case temperature

25.0 °C Threshold current

6.1 A

Current at

20.0 W 37.0

Slope efficiency

0.65 W/A

Voltage at

20.0 W 1.91

Total efficiency at

20.0 W 28.2


Wavelength at

20.0 W 807.1 nm Resistance

0.0077

Spectral width (FWHM) at

20.0 W 2.2 nm



Device type: TH-C1720-F6 N 10045 Date: 09/02/2001 Conditions: P = 20W Spectral Width(FWHM): 2.2 nm Temp = 25C (Internal sensor) Relative intensity 795.0 800.0 805.0 Wavelength (nm) 810.0 815.0 820.0

♦ THOMSON-CSF LASER DIODES


Device type:

TH-C1720-F6

Serial number : 10046

Date: 09/02/2001

Case temperature 25.0 Threshold current °C 6.1 A Current at 20.0 W 36.4 Slope efficiency 0.68 W/A Voltage at Total efficiency at 20.0 W 28.8 20.0 W 1.91 % Wavelength at 20.0 W 807.1 Resistance 0.0079 Spectral width (FWHM) at 20.0 W 2.1 nm



FM MS3121 Ed0 du 13/01/2000 par BP

Checked by:



Operator:

G.DAMEROSE

Device type: TH-C1720-F6 N 10046 Date: 09/02/2001 Conditions: P = 20W Spectral Width(FWHM): 2.1 nm Temp = 25C (Internal sensor) Relative intensity 795.0 805.0 Wavelength (nm) 800.0 810.0 815.0 820.0

04/02/99

OMMUNICATION

DIRECTION FOR USE TH-C1720-F6

The schematic of the THOMSON-CSF LASER DIODES TH-C1720-F6high power fiber-coupled laser array is done on the Data Sheet. Please refer to this schematic for connecting.

COOLING:

- The TH-C1720-F6 is passively cooled. Work temperature is 25°C internal thermal sensor.
- The thermal sensor $(25^{\circ}\text{C}/10\text{k}\Omega)$, see diagram enclosed) is inside, located near the laser diode bar.
- Thermal contact:

The TH-C1720-F6 needs to be fixed on the cooling system using the six 3.5 mm holes of his package. The cooling system must be efficient on the total surface of this package.

We recommend to use only indium sheet (no thermal grease).

Ensure to have a good thermal contact between the TH-C1720-F6 case and the cooling system. (typical: no more than 10°C between the internal thermal sensor indication and the case temperature).

CW- CURRENT POWER SUPPLY:

- THOMSON-CSF LASER DIODES recommends a 50A-5V CW current power supply.
- Electric cables needs to have the right diameter regarding to the driving current.
- A "standby" button witch provide a short-circuit between (+) and (-) output is recommended.

OPTICAL FIBER:

- The optical fiber is the most fragile part of the component.
- Never try pulling the fiber out of the package.
- Don't curve it excessively: minimum 167mm bend radius for long term use at ambient, and 100mm for short term use.

SMA 905 CONNECTOR:

- Take care: don't skim or touch lightly the end optical polished and coated face with hands or any metallic tool.
- Inspect the end face with binocular and lightly clean it if necessary using only optical cleaning tools and products.
- Never increase fiber-coupled laser diodes power with a dirty connector end face. Please contact THOMSON-CSF LASER DIODES if the connector is polluted or scratched.
- Replace plastic cap after use.
- Contact THOMSON-CSF LASER DIODES for any information, or for connecting fiber to fiber.

OPERATION:

- Always use anti-static bracelet.
- Withdraw plastic cap from the fiber end connector.
- Check current power supply: Decrease programmed current to zero before connecting the fiber coupled laser diode.
- Withdraw the short-circuit between cathode and anode.
- Connect power supply cables (+) et (-) respectively on anode and cathode (M3 screw).
- Start running the cooling system.
- Increase current at approximately 0.7A, the power supply must indicate more than 1Volt (check connection in case not)
- Continue increasing current to nominal current (not more 1A/sec.).
- Check temperature stability (25°C).
- Never run over absolute maximum ratings indicated on DATA-SHEET.

END OF OPERATION:

- Decrease current to zero.
- Switch "standby" button or replace short circuit between cathode and anode
- Stop cooling system and replace plastic cap on fiber end

TH-C1715-F4/TH-C1720-F6/TH-C1722-F9

HIGH POWER FIBER COUPLED LASER DIODES

DESCRIPTION

The TH-C17xx-Fy series are high optical power fiber coupled laser diode sources. CW power delivery from 15W to 22W are ideal for applications which request high brightness sources like for efficient pumping solid state lasers, medecine, material processing, micromachining.

The optical power is delivered through a single multimode fiber terminated by a SMA connector. These products integrate ultimate LIMO microoptics. Small fiber diameter and low numerical aperture lead to high brightness and high optical power density.


The diode bar structure use quantum well technology which gives high efficiency and reliability.



- 15W CW, 20W CW and 22W CW optical output power
- Optical delivery through SMA 905 connector (male)
- Optical fiber 1.5m long, 0.22 N.A.
- · Conductively cooled package
- Highly reproducible MOCVD process
- Efficient LIMO microoptics

SPECIFICATIONS






Note:

- Variation of wavelength is approximately 0.26 to 0.3 nm/°C
- Standard wavelength is 808nm
- Tolerance on wavelength is +/- 4nm (+/- 3nm on request)
- Spectral width is < 3nm
- Other wavelength selections are available, on request, in the range of 795nm to 980nm
- Other optical fiber is available, on request, with 0.16 N.A.

September 1999 1/2






ABSOLUTE MAXIMUM RATINGS

PARAMETERS	TH-C1715-F4	TH-C1720-F6	TH-C1722-F9	UNITS
CW output power	16	21	23	Watt
Reverse voltage	3	3	3	Volt
Case Operating temperature	+5 to +35	+5 to +35	+5 to +35	°C
Storage temperature	-30 to +80	-30 to +80	-30 to +80	°C

Note: Operation at temperature below dew point requests to use dry N2 environment

PACKAGE SPECIFICATION:

- dimensions are in mm
- standard tolerances are ± 0.2 mm



For further information please contact:

THOMSON-CSF LASER DIODES - Route Départementale 128 - BP 46 - 91401 ORSAY Cedex / France

Tel (33) 1 69 33 06 61

Fax: (33) 1 69 33 06 62


E-mail: infotld@tld.thomson-csf.com

http:\\www.laser-diodes.thomson-csf.com

Information furnished is believed to be accurate and reliable. However THOMSON-CSF LASER DIODES assumes no responsability for the consequences of use of such information nor for any infringement or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of THOMSON-CSF LASER DIODES. Specifications mentioned in this publication are subjected to change without notice. This publication supersedes and replaces all informations previously supplied. THOMSON-CSF LASER DIODES products are not authorized for use as critical components in life support devices or systems without express written approval from THOMSON-CSF LASER DIODES. @ 1998 THOMSON-CSF LASER DIODES - Printed in France - All rights reserved.



THERMAL SENSOR



THOMSON-CSF LASER DIODES